



- Robust and silent
- Automatic search for the first trough
- Maximum respect for the dough's structure
- Automatic unloading
- Compact
- Two trough sizes available
- Fitted with sockets to connect a moulder and divider









SPECIFICATIONS

Synthetic felt troughs			•
Automatic search for the first trough •			
Folding rounding tray			•
Germicidal UV lamp with protection and air extractor			•
Reference trough			•
Motor power in kW			0.25
		Standard troughs	Wide troughs
	Net weight (in kg)	500	500
	Maximum weight of dough pieces in grams	650	950
	Length x width of troughs in cm	106 x 14	106 x 16
	Total number of troughs	67	53
	Number of usable troughs	46	32
350 g* dough pieces	Number of dough pieces per trough	6	6
	Maximum capacity	402	318
	Usable capacity in a continuous process	276	192
550 g* dough pieces	Number of dough pieces per trough	5	5
	Maximum capacity	335	265
	Usable capacity in a continuous process	230	160
750 g* dough pieces	Number of dough pieces per trough	n/a	4
	Maximum capacity	n/a	7
	Usable capacity in a continuous process	n/a	128
950 g* dough pieces	Number of dough pieces per trough	n/a	3
	Maximum capacity	n/a	159
	Usable capacity in a continuous process	n/a	96

TECHNICAL SPECIFICATIONS

Power supply	230V three-phase,400V three-phase
Dough piece discharge belt	Internal , External,External long



Type of outlet	Left ,Right
Troughs	Standard,Large

MAIN STRENGTHS

Options (Additional cost)



Two three-phase power sockets

Facilitates the connection of moulder and divider.



Foot control, Adjustable unloading speed, Double outfeed, Synthetic fabric troughs

Bronze ring gear wheel

Reduces friction and extends service life.



Controls (right/left)

Simple and ergonomic



UV lamp and air extractor

Germicidal UV lamp with protection and air extractor Sterilises the proofing area and extracts moisture. Hygiene Smooth inside walls Stainless steel exterior covers Flour recovery bins



Lever on the side

Allows the proofer to be used at full capacity.



Automatic search for the first trough

Ease of use and appreciable time savings. No more need for a prolonged button press by the operator to find the first loaded dough piece. With a press of a button, the machine will do it for you.

